


MVF90D Series flow

Time in seconds to evacuate to vacuum level (Sec/1000L)

Model	Vacuum level (-kPa)									
	0	10	20	30	40	50	60	70	80	90
MVF90D-20	0	12	31	69	154	269	431	688	1169	2680
MVF90D-30	0	8	21	46	103	179	288	458	779	1787
MVF90D-40	0	6	16	35	79	139	223	355	603	1383
MVF90D-50	0	5	13	29	65	113	182	289	492	1128
MVF90D-60	0	4	12	26	57	100	160	256	435	997



Vacuum flow at different Vacuum levels (L/Min)

Model	Vacuum level (-kPa)									
	0	10	20	30	40	50	60	70	80	90
MVF90D-20	568	328	213	104	74	58	38	22	10	0
MVF90D-30	852	492	319	156	110	86	58	34	14	0
MVF90D-40	1101	636	412	202	143	112	74	43	19	0
MVF90D-50	1349	779	505	247	175	137	91	53	23	0
MVF90D-60	1527	882	572	280	198	155	103	60	26	0

